

# DAIRY POWER

## Cleaning and hygiene solutions for the dairy industry



DAIRY HYGIENE PRODUCT RANGE



TEAT CARE SOLUTIONS

Dairy Power Masidyne

Iodophor teat sanitiser

Medicated formulation containing glycerine and lanolin. Glycerine 46g/L and lanolin 16g/L. Can be used as a teat dip or spray. Iodine aids in the control of mastitis while the glycerine and lanolin keep the teats in good condition.

20 litre drum	P/C 7302231
110 litre drum	P/C 7302232
200 litre drum	P/C 7302233
1000 litre IBC	P/C 7302234
APVMA approval	49122

Dairy Power Glysoft

Udder emollient

An emollient containing sorbitol and glycerine, sorbitol 643g/L and glycerine 113g/L. When added to an iodine teat dip or spray it enhances teat skin condition particularly in winter.

20 litre drum	P/C 6821020
200 litre drum	P/C 6821200
1000 litre IBC	P/C 6821911
APVMA approval	56788

Dairy Power Ready-Dyne

Iodophor teat sanitiser

A ready to use iodine based pH adjusted teat dip and spray formulated for the control of mastitis. The product contains a high amount of lanolin, glycerine and sorbitol to help keep teats in good condition, lanolin 4g/L glycerine 11.5g/L and sorbitol 105g/L. The ideal product to use in areas where water quality is a problem.

200 litre drum	P/C 7302235
1000 litre IBC	P/C 7302236
APVMA approval	56087

Dairy Power Maspray

Disinfectant teat dip and spray

Chlorhexidine gluconate based teat disinfectant that aids in the control of mastitis causing organisms. Contains glycerine 454g/L to keep teats in good condition.

20 litre drum	P/C 15034
110 litre drum	P/C 6836110
APVMA approval	49123

Dairy Power Teat Care

Antiseptic teat ointment

Formulated cream with chlorhexidine and cetrimide to help prevent mastitis, including glycerine (30g/l) to soften and restore the skin condition.

4 x 1 litre carton	P/C 17156
APVMA approval	47669

Dairy Power Tail Paint

Tail paint

Dairy Power Tail Paint is a non- irritant, weather resistant animal marker.

Bright and easy to see colours.

Blue, carton of 12x 500mL cans	P/C 7864006
Green, carton of 12x 500mL cans	P/C 7866006
Orange, carton of 12x 500mL cans	P/C 7862006
Pink, carton of 12x 500mL cans	P/C 7861006
Red, carton of 12x 500mL cans	P/C 7865006
Yellow, carton of 12x 500mL cans	P/C 7863006
Can Holster, each	P/C 7868001

CLEANING AND SANITISING SOLUTIONS – ACID

Dairy Power CB Acid

Heavy duty acid

Highly concentrated liquid acid cleaner formulated from a blend of phosphoric acid, wetting agents and effective in the removal of baked on milkstone and hard water deposits. Low foaming formula makes it suitable for use in all milking plants and vats as well as in autowash units where liquids are preferred.

20 litre drum	P/C 16632
110 litre drum	P/C 6809110
APVMA approval	49189

Dairy Power Acid Liquid

Acid Liquid detergent

Dairy Power Acid Liquid is used for the CIP removal of milkstone and other organic or inorganic scale from stainless steel equipment. Dairy Power Acid Liquid is a clear, colourless, mobile liquid with a nitric acid odour.

20 litre drum	P/C 7300524
200 litre drum	P/C 7300522
APVMA approval	64949

Dairy Power Acid Powder

Powdered Acid

Dairy Power Acid Powder is a powerful acidic detergent specially formulated to remove deposits of hard water salts, denatured protein and milkstone. These deposits are not readily removed by caustic based detergents and if not removed can reduce performance of heat exchangers and provide a place where microorganisms can multiply. Dairy Power Acid Powder is a pink, crystalline, practically odourless powder.

20 kg pail	P/C 7300565
APVMA approval	64926

Dairy Power Flexi-Klenz

Acid detergent sanitiser

A high performance, acidic detergent sanitiser for the cleaning and sanitising of high velocity dairy milking plants and storage equipment. Dairy Power Flexi-Klenz has proven sanitising technology and is free of quaternary ammonium compounds (QAC's).

20 litre drum	P/C 7302624
110 Litre drum	P/C 7302625
200 Litre drum	P/C 7302626
1000 Litre IBC	P/C 7302627
APVMA approval	84187

Dairy Power Aquasan

Concentrate

Acid detergent sanitiser

A concentrated low foaming, acidic cleaner/sanitiser for use in high velocity dairy milking machines as well as milk storage vats as a one-step operation.

20 litre drum	P/C 7302321
110 Litre drum	P/C 7302322
200 Litre drum	P/C 7302323
1000 Litre IBC	P/C 7302324
APVMA approval	83318

Dairy Power Defender

Low foam acid sanitiser

Low foam acid anionic sanitiser with high biocidal activity suitable for use in most milking plants and vats as a contact sanitiser and where vat and line autowash units are installed. Can be used in hot or cold water.

20 litre drum	P/C 15354
110 litre drum	P/C 6815110
200 litre drum	P/C 6815200
1000 Litre IBC	P/C 7301322
APVMA approval	49190

Dairy Power Supersan

Low foam acid sanitiser

Dairy Power Supersan is a low foam, phosphate-free, acid sanitiser. It contains no iodine and can be used in hot or cold water. Suitable for use in most automatic vat and line wash systems.

20 litre Drum	P/C 7300529
200 litre Drum	P/C 7300527
APVMA approval	65176

CLEANING SOLUTIONS – ALKALI

Dairy Power Auto-Kleen

Heavy duty low foam alkaline cleaner

Low foaming heavy duty caustic based liquid circulation cleaner designed to remove most fat and proteinaceous soils. Suitable for use in cold climates with in most autowash units, vats and milking plants where liquids may be automatically dispensed.

20 litre drum	P/C 7219020
110 litre drum	P/C 7219110
200 litre drum	P/C 7219200
APVMA approval	52224

Dairy Power Back-Up

Heavy duty low foam alkaline cleaner

Specifically formulated for stubborn soils. Low foaming blend of caustic, surfactants, sequestering agents and soil suspending agents quickly penetrate, remove and suspend organic soils from the milking plant. Suitable for use with most autowash units, vats and milking plants where liquids can be automatically dispensed for safety.

20 litre drum	P/C 14968CT
200 litre drum	P/C 6803200
APVMA approval	49183

Dairy Power Clenex

General low foam powder detergent

General purpose low foaming detergent suitable for cleaning most milking plants, vats and parts. Balanced formula and high levels of softening agent ensure excellent rinsability and enable it to be used in hard water conditions. Safe to use on all equipment. Helps prevent the formation of milkstone and scale deposits.

20 kg bag	P/C 14594
APVMA approval	49185

Dairy Power Inline

Heavy duty low foam alkali cleaner

Formulated for use on farms for cleaning milking equipment and in dairy processing for the cleaning of cream pasteurisers, plate heat exchangers, silos, vats, chillers and road tankers. Inline is suitable for use in recirculating systems and is effective in hard water conditions.

20 kg pail	P/C 16290
20 kg bag	P/C 16288
APVMA approval	49191

CLEANING & SANITISING SOLUTIONS – SPECIALITY

Dairy Power Assist

Low foam pre-cleaning additive

Low foam wetting agent which softens and breaks up milk deposits in the post milking rinse step preventing milkstone formation during the hot wash. Particularly desirable for use in low line plants, large bore milk lines and where water quality or hardness is extreme.

20 litre drum	P/C 14772
110 litre drum	P/C 6797110
APVMA approval	49184

Dairy Power Impact

Chlorinated caustic bomb

Low foaming chlorinated caustic detergent powder formulated for use as a weekly or remedial bomb cleaner. Very effective in removing stubborn proteinaceous and heavy soil build-ups in dairy plants.

10 kg pail	P/C 17242
20 kg pail	P/C 6827020
APVMA approval	49181

Dairy Power Eze-Fome

High foam alkaline detergent

Chlorinated high foaming alkaline liquid cleaner. Can be used for manual cleaning, parts washing and can also be foamed onto surfaces using a hydrofoamer. Particularly suited for the removal of fatty and proteinaceous soils from milk vats, bails and receival cans.

10 litre drum	P/C 6818010
APVMA approval	49182

Oxysept Agri

Peroxyacetic Acid Sanitiser

Oxysept Agri is a stabilized peroxyacetic acid sanitiser. It is used to sanitise hard non-porous surfaces of automated milking equipment between cow milkings. The stabilized peroxyacetic acid ensures powerful sanitising properties against a broad range of bacteria.

20 Litre Drum	P/C 7301262
110 Litre Drum	P/C 7301263
APVMA approval	70095



Everywhere It Matters.



## Advancing milk quality through industry-leading service and expertise

The quality of the milk that you produce is vital in maintaining the profitability of your dairy operation.

Made in Australia, ECOLAB offers a complete range of teat care sprays to protect your herd, along with cleaners and sanitisers that clean milking machines, pipes, vats, coolers and holding tanks that transport your raw milk at the dairy.

Our local support team includes dairy specialists, formulation chemists and application engineers who are all on hand, to help you optimise your dairy operation and support your day to day, dairy hygiene and animal health challenges.

When you partner with ECOLAB, you partner with a knowledgeable and experienced team of milk quality experts whose role it is, to help you supply the best quality milk possible.

### **Ecolab Australia Customer Service**

Tel: 1 800 022 002

Email: [ausecolink@ecolab.com](mailto:ausecolink@ecolab.com)